

Registration certificate

№ ФСР 2009/04140, № ФСР 2011/11388, № ФСР2011/12132, № ФСР 2012/13325.

Patent Russia: № 111762, № 2306150



Additional functions of sterilizers with UV-lamps



HTHER BY HOME

DEZAR

Filtering of air flow

Particles more than 10 microns: dust, pollen, plant spores, mildew, fumes of sterilization liquids, sprays.

Changeable Air Filter CAF - KRONT

260x90x5 mm

Filtering synthetic material (100 % polyester)

Plug-in filtering block



Clearance of air flow from toxic chemical admixture

Anesthetic gases, antibiotics, formaldehydes, ammonia, alcohols, hormone, washing, disinfection and sterilizing liquids, pair acids and alkalis, carbon oxide (CO) and nitrogen (NO) etc.

Changeable Charcoal Filter CCF - KRONT

260x90x5 mm

Reinforcing material

Activated Charcoal material

Reinforcing material
(pre-filtering for dust 10 mk)

Two strong fixing-catches allow installing plug-in filtering block on to trunk of sterilizer.

Filtering block consists of:

- · security grid,
- air filter or combined charcoal filter,
- grid filter holding for fixing filter with 2 strong catch.

Do not need any tools for assembling and installing the filtering block and exchanging the filter.

Model	DEZAR-2 (ORUBN-2-01-KRONT) WALL MOUNTING	DEZAR-3 (ORUBN-3-3-KRONT) WALL MOUNTING	DEZAR-5 (ORUBN-3-5-KRONT) WALL MOUNTING
		DEZAR-4 (ORUBP-3-3-KRONT) MOBILE	DEZAR-7 (ORUBP-3-5-KRONT) MOBILE
Class room	III - V	II - V	1-V
Germicidal Efficiency, %	95,0	99,0	99,9
Productivity, m³/hour	70	100	100

